

## **Product information**

# mzr-11508X1 · High performance pump series



## **Description**

The micro annular gear pump mzr-11508X1 is equipped with tungsten carbide rotors and bear-ings. Hard construction material and precision manufacturing techniques guarantee excellent dosage precision, high service life and wear resistance for low volume dosage of non-lubricating liquids. Driven by a high-power DC-motor the pump has a compact design and covers the flow range from 0.19 ml/min to 1152 ml/min. The mzr-11508X1 is suitable for continuous delivery and discrete dosage of high viscosity liquids. It achieves high differential pressures and provides a low pulsation flow. Its robustness and the available accessories make it suitable for challenging applications.

#### **Advantages**

- High dosage precision precision CV < 1% at low volumes</li>
- Long service life wear-resistant tungsten carbide
- Broad viscosity range methanol, water, solvents, adhesives, grease, gel
- Dynamic precision motor brushless DC-motor with encoder

- Compact dimensions length 265 mm
- High differential pressures achievable even for low viscosity liquids
- Low pulsation delivery, low shear stress rotary micro annular gear technology

## **Applications**

- Chemical processing
- Industrial and plant engineering
- Packaging
- Medical and pharmaceutical industry
- Mini plant technology

- Spraying
- Dispensing of adhesives
- Ink and paint dosage
- Vacuum applications



| Technical data              |  |
|-----------------------------|--|
| Flow rate                   | 0.19 - 1,152 ml/min  |
| Smallest dosage volume      | 100 µl   |
| Displacement volume         | 192 µl   |
| Differential pressure range | 0 – 30 bar (435 psi)   |
| Maximum inlet pressure      | 10 bar (145 psi)   |
| Liquid temperature range    | -5 +60 °C (-20 +150 °C *) (+23 +140 °F (-4 +302 °F))   |
| Viscosity range             | 0.3 – 50,000 (100,000 *) mPas  |
| Precision CV                | < 1% (Coefficient of variation CV)   |
| Velocity range              | 1 - 6,000 rpm  |
| Fluid connection            | 3/8" NPT internal thread, lateral; optional 3/8" NPT internal thread, frontal  |
| Wetted parts                | stainless steel 316L (1.4435), tungsten carbide Ni-based; shaft seal: graphite-reinforced PTFE, alloy C276 (2.4819); static seals: FPM, optional: EPDM, FFPM |
| Motor                       | brushless DC-servomotor, IP 54, winding 36 V DC, output power 201 W, max. continuous torque 192 mNm  |
| Positioning                 | 1000 counts per turn, analog hall sensors  |
| Interface                   | motor cable length 2 m, 6-pole plug for motor winding, 12-pole plug for encoder and hall sensors   |
| Dimensions (L x W x H)      | 265 x 100 x 109 mm   |
| Weight                      | approx. 4,500 g  |
| Remarks                     | * with optional heat insulation or heating module, Customized solutions on request.  |

#### Notice

Even if single parameters are within the indicated performance range of technical data, certain parameter combinations may not be achievable. Single parameters may exceed their indicated performance range under adequate circumstances. For detailed evaluation please contact HNP Mikrosysteme. Actual performance may vary. Specifications are subject to change without notice.


## Accessories

- S-BL
- Reduction gear
- Reservoir Plastic
- Double shell heating module


- mzr-Touch Control
- Heat insulation module
- Electrical heating module



## **Dimensions**



## Flow charts



## **Patents and trademarks**

Micro annular gear pumps (and housings) are protected by assigned patents: EP 1 354 135 B1; US 7,698,818 B2; DE 10 2011 001 041 B4; CN 103 348 141 B; US 10,012,220 B2; CN 103 732 921 B; US 9,404,492 B2; US 6,520,757 B1. HNPM $^{\mathbb{R}}$ , mzr $^{\mathbb{R}}$ , MoDoS $^{\mathbb{R}}$ ,  $\mu$ -Clamp $^{\mathbb{R}}$ ,  $\mu$ Dispense $^{\mathbb{R}}$ , Centifluidic Technologies $^{\mathbb{R}}$ , LiquiDoS $^{\mathbb{R}}$ , smartDoS $^{\mathbb{R}}$ , ColorDoS $^{\mathbb{R}}$  are registered German trademarks of HNP Mikrosysteme GmbH.

## Contact

HNP Mikrosysteme GmbH Bleicherufer 25 19053 Schwerin Germany

ast update 2019/10

T +49 385 52190-300 F +49 385 52190-333 info@hnp-mikrosysteme.de